


KEMET Part Number: SSHB10H-11054
(UALSB111054000)

KEMET, SSHB10H, AC Line Filters, Dual Mode, 5400 uH



Dimensions

| | |
|-----------|----------------|
| L | 22mm MAX |
| T | 17mm MAX |
| H | 15.5mm MAX |
| LL | 3.5mm +/-0.5mm |
| S | 13mm +/-0.5mm |

Packaging Specifications

| | |
|----------------------------|------|
| Packaging: | Tray |
| Packaging Quantity: | 300 |
| Weight: | 10 g |

General Information

| | |
|-----------------------|--------------------------------|
| Series: | SSHB10H |
| Style: | Through-Hole |
| RoHS: | Yes |
| Notes: | Marking: 11 Lot No. |
| Miscellaneous: | Temperature Rise Maximum: 55 K |

Specifications

| | |
|---------------------------|-----------------|
| Voltage AC: | 250 VAC |
| Inductance: | 5.4 mH (10 kHz) |
| Current: | 1.1 A |
| Temperature Range: | -25/+130°C |
| DC Resistance: | 390 mOhms |