


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00106	Connector, dc plug, 2.35x0.7xL18.5 mm, brass nickel plated, spring contacts	1	
2	30-00003	Wire, 2C BC, 24 AWG, UL2468, 300V, 80C, 3.6 mm, VW-1, PVC, 76A	1	
3	24-00047	Overmold, PVC	1	black



Notes:

Electical requirement: 500 mA, 36 Vdc

Hi-Pot test: 600 Vac, 0.5 mA, 1 second

Wiring Diagram	
50-00106	wire color
center	black with stripe
sleeve	black

Revision:	Date:	Description:	Prepared:	Notes:	<h1>TENSILITY</h1> <p>tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com</p>				
A	1/19/2009	Re-issue CUI spec as Tensility	GL <small>Digitally signed by GL Date: 2016.12.09 15:18:27 -0800'</small>	RoHS compliant					
A1	10/12/2009	Added overmold dimensions; insulator color corrected	Verified: DN <small>Digitally signed by DN Date: 2016.12.09 15:46:31 -0800'</small>	Function test: no open, no short circuit, no intermittent					
A2	8/31/2011	Updated description, connector, and wire information	Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description: Cable, 1830 mm, 2.35x0.7x9.5 mm, 50-00106 dc plug to stripped tinned, 24 AWG, 30-00003 wire					
A3	6/14/2012	Updated connector description							
A4	12/9/2016	Corrected tolerance typo			<table border="1"> <tr> <td>Size:</td> <td>Part number:</td> </tr> <tr> <td>A</td> <td>053-0191R (CA-2192)</td> </tr> </table>	Size:	Part number:	A	053-0191R (CA-2192)
Size:	Part number:								
A	053-0191R (CA-2192)								
Scale: 1:1				Sheet 1 of 1					