




DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENDING VERPLICHT.
 THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

REV.	DATE	DESCRIPTION	BY	C'K'D'
00	14.08.97	REDRAWN FROM DRAWING BSA 062109 SHEET 1	S.V.D.	



DRILLING HOLE PATTERN

MATERIAL :

BODY : NYLON, UL94V-2, COLOUR : BLACK
 CONTACTS : CONTACT BODY : BRASS, GOLD OR TIN PLATED
 INNER SPRING : BERYLLIUM COPPER, GOLD OR NICKEL PLATED

PERFORMANCE CHARACTERISTICS :

OPERATING TEMPERATURE : -55°C TO 105°C
 INSULATING RESISTANCE : 5000 MΩ MIN.
 TEST POTENTIAL : 2000 VAC

NOTES :

- CONNECTOR SUPPLIED FULLY LOADED WITH MACHINED SOCKET CONTACTS.
GOLD PLATED : SMS2GE3 ; GOLD FLASH : SMS2GE3J ; TIN PLATED : SMS2GE3T
- MATING PART SMS2P1 PLUG
- PC-BOARD THICKNESS : 2.4 MM

BS,A , 202362,001,00

GEN. ST.	01	02	03	04	05	06	07	08	0D	50	60	70	80	90																	
INT. ST.	10	11	12	13	14	18	20	31	32	33	34	38	39	40	42	43	44	45	46	48	56	70	72	73	75	76	81	82	83	84	88

1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN	APPR. DRAFT CHECKED	DATE 14-08-97	SIGN. S.Van Dessel	SMS QIKMATE STRAIGHT FEMALE REC. WITH MACH. CONT.	
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	PROD. MGR. PR. ENG. MGR. PR. MGT. MGR.			CAT. No. SMS2GE3*	
ALL DIMENSIONS IN MM 	REFERENCES / REFERENTIES			SOURIAU Route Nationale 23 72470 CHAMPAGNE	
ALLE AFMETINGEN IN MM				SCALE 2/1	
				BS,A , 202362,001,00 DRAWING NR. CUSTOMER DRAWING	