

# LC3

## High Power Resonant Capacitors



### FEATURES

High AC Voltage - High Current

### APPLICATIONS

Induction Heating - Tank Circuits

KVAR	300
CAPACITANCE TOLERANCE	+/-10%
MAXIMUM CORE TEMPERATURE	+85°C
SURFACE TEMPERATURE	+45°C (Above 45°C the KVAR rating must be de-rated by 2.25%/°C)
CONSTRUCTION	Self-healing
SELF INDUCTANCE	< 5 nH
DIELECTRIC	Polypropylene
FLAME RETARDANT	UL94V0

### Standard Part Listing

Capacitance (µF)	VAC	IC part number	Maximum RMS current (A)	MAX power kvar	Frequency range (kHz)	ESR (mΩ) 100kHz, +25°C	Dimensions (mm)			Terminal Style
							B	H	L	
0.1	1000	104LC3102KL505HM6	350	300	476-649	1.2	34	50	50	5HM6
0.2	1000	204LC3102KL505HM6	500	300	238-423	1.2	34	50	50	5HM6
0.25	700	254LC3700KL505HM6	500	300	390-530	1.2	34	50	50	5HM6
0.33	700	334LC3700KL505HM6	500	300	295-401	1	34	50	50	5HM6
0.66	700	664LC3700KL505HM6	500	300	147-200	0.8	34	50	50	5HM6
1	600	105LC3600KL505HM6	650	300	132-223	0.5	34	50	50	5HM6
1.2	600	125LC3600KL505HM6	650	300	111-187	0.5	34	50	50	5HM6
1.32	600	135LC3600KL505HM6	650	300	100-170	0.3	34	50	50	5HM6
2.4	500	245LC3500KL505HM6	650	300	80-97	0.2	34	50	50	5HM6
0.25	700	254LC3700K5LM8	500	300	390-530	1.2	34	78	78	5LM8
0.33	700	334LC3700K5LM8	500	300	295-401	1	34	78	78	5LM8
0.66	700	664LC3700K5LM8	500	300	147-200	0.8	34	78	78	5LM8
1	600	105LC3600K5LM8	650	300	132-223	0.5	34	78	78	5LM8
1.2	600	125LC3600K5LM8	650	300	111-187	0.5	34	78	78	5LM8
1.32	600	135LC3600K5LM8	650	300	100-170	0.3	34	78	78	5LM8
2.4	500	245LC3500K5LM8	650	300	80-97	0.2	34	78	78	5LM8
2.6	500	265LC3500K5LM8	650	300	72-85	0.2	34	78	78	5LM8
5	400	505LC3400K5LM8	800	300	59-67	0.1	34	78	78	5LM8

Americas / EU  
Phone: 1-508-996-8561  
Email: cdena@cde.com




Asia  
Phone: 852-2793-0931  
Email: cdeasia@cde.com

# LC3

## High Power Resonant Capacitors



LEAD STYLE: 5HM6, 5LM8



Style	L	H	B	H2	L2	Mounting Holes
5HM6	50+1.0	50+1.0	34+0.5	36	36	M6 Tap
5LM8	78+1.0	78+1.0	34+0.5	62	62	M8 Tap

Tightening Torque: 20Nm MAX







# LC3

## High Power Resonant Capacitors



### Frequency Derating

— Voltage — Current — Power



Americas / EU  
 Phone: 1-508-996-8561  
 Email: cdena@cde.com



Asia  
 Phone: 852-2793-0931  
 Email: cdeasia@cde.com






# LC3

## High Power Resonant Capacitors



### Frequency Derating

— Voltage — Current — Power



Americas / EU  
Phone: 1-508-996-8561  
Email: cdena@cde.com



Asia  
Phone: 852-2793-0931  
Email: cdeasia@cde.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Cornell Dubilier:

[334LC3700K5LM8](#) [664LC3700KL505HM6](#) [204LC3102KL505HM6](#) [135LC3600KL505HM6](#) [254LC3700KL505HM6](#)  
[245LC3500KL505HM6](#) [505LC3400K5LM8](#) [265LC3500K5LM8](#) [125LC3600K5LM8](#) [245LC3500K5LM8](#)  
[664LC3700K5LM8](#) [105LC3600KL505HM6](#) [135LC3600K5LM8](#) [125LC3600KL505HM6](#) [105LC3600K5LM8](#)  
[334LC3700KL505HM6](#) [254LC3700K5LM8](#)