


# Wiha PocketStar.

Press one button for the correct key.



The unique opening mechanism facilitates an easy selection of the desired key size.

The Wiha PocketStar fold out offers optimum handling and a wide variety of uses, which are expressed in the form of many practical details.

The ingenious opening mechanism facilitates the simple selection of the required key size from the glass-fibre-reinforced holder.

Wiha solved an important demand of fold-out users: When turning a key into working position only this one moves. The remaining keys stay where they are.

The various working positions offer universal use:

- In the 180° position, the PocketStar is used as a screwdriver.
- 270° stop limit for using the tool as practical lever for high torques.
- Any position can be set between 90° and 270° for a variety of different work applications.



The 270° stop limit when working on applications with higher safety requirements puts an end to trapped fingers.

All it takes is three swift actions and you have an effective screwdriver: Pull it out of the pouch, press on the button and set the desired blade to 180° as well as 270°.



## Wiha PocketStar.

- Innovative opening mechanism for simple selection of the desired key size
- Particular suitable for use as screwdriver when the blade axis is set at 180° or as practical lever with blade in 270° position
- Ergonomic, glass-fibre-reinforced holder guarantees the easy transfer of even the highest torques
- Can be rotated by any angle between 270° and 90° to save time when working on applications where space is tight
- 270° stop limit for higher safety puts an end to trapped fingers
- Colour-coding system for different drives and dimensional systems delivers great clarity when using several PocketStars
- Covered hex key axes prevents catching on clothes

### For Allen screws (metric).



#### 369R P7 Ball end hex fold out holder PocketStar. With MagicRing®, in large PocketStar, 7 pcs.

- Blade: Chrome-vanadium steel, through hardened, electro-plated.  
 Handle: Ergonomic, reinforced fibreglass housing, 120 mm long.  
 Application: Practical fold out holder for hex screws in the workplace or on the job. Insert screws into or remove from boreholes, especially in difficult to access areas.  
 Extra: Robust casing with eject button for simple and easy key selection. MagicRing® made from spring steel holds all standard screws tight at various angles (available from 3 mm). The ball end enables the user to work at angles up to 25°.

Order-No.	369R P7	5
23031 9	2 2.5 3 4 5 6 8	

#### SB 369R P7 Ball end hex fold out holder PocketStar. With MagicRing®, in large PocketStar, 7 pcs. Blister packed with hanging hole.

Order-No.	SB 369R P7	5
23033 3		

### For Allen screws (metric).



#### 351 PG7 Hex fold out holder PocketStar. In large PocketStar, 7 pcs.

- Blade: Chrome-vanadium steel, through hardened, electro-plated.  
 Handle: Ergonomic, reinforced fibreglass housing, 120 mm long.  
 Application: Practical fold out holder for hex screws in the workplace or on the job.  
 Extra: Robust casing with eject button for simple and easy key selection.

Order-No.	351 PG7	5
23040 1	2 2.5 3 4 5 6 8	

#### SB 351 PG7 Hex fold out holder PocketStar. In large PocketStar, 7 pcs. Blister packed with hanging hole.

Order-No.	SB 351 PG7	5
23041 8		



#### 351 PK7 Hex fold out holder PocketStar. In small PocketStar, 7 pcs.

- Blade: Chrome-vanadium steel, through hardened, electro-plated.  
 Handle: Ergonomic, reinforced fibreglass housing, 95 mm long.  
 Application: Practical fold out holder for hex screws in the workplace or on the job.  
 Extra: Robust casing with eject button for simple and easy key selection.

Order-No.	351 PK7	5
23035 7	1.5 2 2.5 3 4 5 6	

#### SB 351 PK7 Hex fold out holder PocketStar. In small PocketStar, 7 pcs. Blister packed with hanging hole.

Order-No.	SB 351 PK7	5
23037 1		

## Wiha Info

### Colour-coding system:

- red: metric hex blades
- yellow: inch hex blades
- green: TORX® blades
- light green: TORX PLUS® blades

# Wiha PocketStar.

Press one button for the correct key.

## Mixed sets.



### 351 PG9X Fold out holder PocketStar containing assorted keys.

In large PocketStar, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, electro-plated.

Handle: Ergonomic, reinforced fibreglass housing, 120 mm long.

Application: Practical fold out holder for hex, slotted, Phillips and TORX® screws in the workplace or on the job.

Extra: Robust casing with eject button for simple and easy key selection.

Order-No.	Content	Icon
25293 9	351 PG9X	5
①	4,5	
⊕	PH2	
⊗	T10 T15 T20	
●	3 4 5 6	

### SB 351 PG9X Fold out holder PocketStar containing assorted keys.

In large PocketStar, 9 pcs.

Blister packed with hanging hole.

Order-No.	Content	Icon
25295 3	SB 351 PG9X	5



### 351 PK6X Fold out holder PocketStar containing assorted keys.

In small PocketStar, 6 pcs.

Blade: Chrome-vanadium steel, through hardened, electro-plated.

Handle: Ergonomic, reinforced fibreglass housing, 95 mm long.

Application: Practical fold out holder for hex, slotted and Phillips screws in the workplace or on the job.

Extra: Robust casing with eject button for simple and easy key selection.

Order-No.	Content	Icon
24859 8	351 PK6X	5
①	5,5	
⊕	PH2	
●	3 4 5 6	

### SB 351 PK6X Fold out holder PocketStar containing assorted keys.

In small PocketStar, 6 pcs.

Blister packed with hanging hole.

Order-No.	Content	Icon
24861 1	SB 351 PK6X	5

## For TORX® screws.



### 363 P8 TORX® fold out holder PocketStar.

In large PocketStar, 8 pcs.

Blade: Chrome-vanadium steel, through hardened, electro-plated.

Handle: Ergonomic, reinforced fibreglass housing, 120 mm long.

Application: Practical fold out holder for TORX® screws in the workplace or on the job.

Extra: Robust casing with eject button for simple and easy key selection.

Order-No.	Content	Icon
23047 0	363 P8	5
⊗	T9 T10 T15 T20	
	T25 T27 T30 T40	

### SB 363 P8 TORX® fold out holder PocketStar.

In large PocketStar, 8 pcs.

Blister packed with hanging hole.

Order-No.	Content	Icon
23049 4	SB 363 P8	5



### 363 P7 TORX® fold out holder PocketStar.

In small PocketStar, 7 pcs.

Blade: Chrome-vanadium steel, through hardened, electro-plated.

Handle: Ergonomic, reinforced fibreglass housing, 95 mm long.

Application: Practical fold out holder for TORX® screws in the workplace or on the job.

Extra: Robust casing with eject button for simple and easy key selection.

Order-No.	Content	Icon
23051 7	363 P7	5
⊗	T7 T8 T9 T10	
	T15 T20 T25	

### SB 363 P7 TORX® fold out holder PocketStar.

In small PocketStar, 7 pcs.

Blister packed with hanging hole.

Order-No.	Content	Icon
23053 1	SB 363 P7	5

## For TORX® Tamper Resistant screws.



### 363TR P8 TORX® Tamper Resistant fold out holder PocketStar.

In large PocketStar, 8 pcs.

Blade: Chrome-vanadium steel, through hardened, electro-plated.

Handle: Ergonomic, reinforced fibreglass housing, 120 mm long.

Application: Practical fold out holder for TORX® Tamper Resistant (with security pin) screws in the workplace or on the job.

Extra: Robust casing with eject button for simple and easy key selection. Borehole in every blade tip.

Order-No.	Content	Icon
25130 7	363TR P8	5
⊗	T9H T10H T15H T20H	
	T25H T27H T30H T40H	

### SB 363TR P8 TORX® Tamper Resistant fold out holder PocketStar.

In large PocketStar, 8 pcs.

Blister packed with hanging hole.

Order-No.	Content	Icon
25166 7	SB 363TR P8	5



### 363TR P7 TORX® Tamper Resistant fold out holder PocketStar.

In small PocketStar, 7 pcs.

Blade: Chrome-vanadium steel, through hardened, electro-plated.

Handle: Ergonomic, reinforced fibreglass housing, 95 mm long.

Application: Practical fold out holder for TORX® Tamper Resistant (with security pin) screws in the workplace or on the job.

Extra: Robust casing with eject button for simple and easy key selection. Borehole in every blade tip.

Order-No.	Content	Icon
25128 4	363TR P7	5
⊗	T7H T8H T9H T10H	
	T15H T20H T25H	

### SB 363TR P7 TORX® Tamper Resistant fold out holder PocketStar.

In small PocketStar, 7 pcs.

Blister packed with hanging hole.

Order-No.	Content	Icon
25164 2	SB 363TR P7	5

## Displays.



### 351 PG7 VH1 Display hex fold out holder PocketStar.

In large PocketStar, 7 pcs.

Carton display with 10 pieces.

Order-No.	Content	Icon
23502 4	10 x 351 PG7	2 - 8
		1



### 351 PG9X VH1 Display fold out holder PocketStar containing assorted keys.

In large PocketStar, 9 pcs.

Carton display with 10 pieces.

Order-No.	Content	Icon
25297 7	10 x 351 PG9X	1



### 363 P8 VH1 Display TORX® fold out holder PocketStar.


In large PocketStar, 8 pcs.

Carton display with 10 pieces.

Order-No.	Content	Icon
23503 1	10 x 363 P8	T9 - T40
		1

# Wiha Mini PocketStar.

The smallest blade at the push of a button.



The unique opening mechanism facilitates an easy selection of the desired key size.

Who hasn't spent ages looking for the small SW 0.9 hex key or for other small keys?

Wiha has developed an extremely smart solution to solve exactly this problem: the Mini PocketStar, a small practical helper that is an absolute must in the toolbox of every service and customer-service engineer.

Regardless of whether replacing a proximity switch or pneumatic control unit, or whether adjusting the sensitivity of a light barrier. With the Mini PocketStar, all keys are within reach.



Small but effective.  
The Mini PocketStar from Wiha is the smart helper for service engineers and for DIY use.



The 180° stop limit when working on applications with higher safety requirements puts an end to trapped fingers.



## Wiha Mini PocketStar.

- All small keys are held together in the Mini PocketStar. Not a single blade is lost
- Each of the 8 blades can be used as screwdriver when set at 180° and as tool with lever arm when set at 90°
- The glass-fibre-reinforced polyamide holder ensures that the Mini PocketStar withstands every stress unscathed
- Of course, the smallest PocketStar also has the same special functions as the "big" PocketStars

### Mixed sets.



**SB 351 PM8X** Hex fold out holder Mini PocketStar.  
With additional blades, 8 pcs.  
Blister packed.

Blade: Chrome-vanadium steel, through hardened, electro-plated.  
Handle: Ergonomic, reinforced fibreglass housing, 55 mm long.  
Application: Practical fold out holder for mini keys so they no longer get lost. Particularly suitable for use with the smallest screws, e.g. when tightening screws or for the accurate setting of sensors.  
Extra: Robust casing with eject button for simple and easy key selection. Hanging loop with matching snap-hook.

Order-No.	SB 351 PM8X	5
●	0.7 0.9 1.3 1.5 2.0	
⊕	1.5 2.0	
⊕	PH00	

### Mixed sets.



**SB 363 PM8X** TORX® fold out holder Mini PocketStar.  
With additional blades, 8 pcs.  
Blister packed.

Blade: Chrome-vanadium steel, through hardened, electro-plated.  
Handle: Ergonomic, reinforced fibreglass housing, 55 mm long.  
Application: Practical fold out holder for mini keys so they no longer get lost. Particularly suitable for use with the smallest screws, e.g. when tightening screws or for the accurate setting of sensors.  
Extra: Robust casing with eject button for simple and easy key selection. Hanging loop with matching snap-hook.

Order-No.	SB 363 PM8X	5
●	T4 T5 T6 T7	
⊕	1.5 2.0	
⊕	PH00	
●	2.0	

# Wiha ComfortGrip T-handle.

Soft zones for maximum working comfort.




Side blade with through blade.

The new Wiha T-handle with through blade for additional side blade features soft zones for the comfortable transmission of high torques.

Due to their ergonomic design, these handles are comfortable to hold. Fewer pressure points and less strain on the user mean that these tools are a pleasure to use.

When using the side blade, a supporting hand on the handle produces additional stability, which prevents the blade from suddenly slipping out of the screw head. This is better for both blade and screw.

The hole in the handle can be used for shop storage.



No screw can resist. The powerful Wiha ComfortGrip is quick and comfortable to use and even loosens screws that have been glued into position.



A tool that is a pleasure to use. Using the side blade for even greater torque, a supporting hand stabilises the handle and prevents the blade from slipping.



Black soft zones in the handle for comfortable working.



Chrome-plated blade for optimum corrosion protection.



## Wiha ComfortGrip T-handle.

- The integrated side blade is particularly useful when loosening or tightening screws that are rusted-in, glued into position or particularly hard to move
- The through blade withstands even the highest stresses
- Distinctive soft zones on the ergonomic handle for the comfortable transmission of even high torques
- Handle-size concept with three handle shapes designed for maximum ease of use and for applying just the right amount of torque
- The new colour-coding system for the handles couldn't be clearer:  
**Red:** metric hex blades  
**Green:** TORX® profiles
- Matt chrome-plated blades guarantee optimum corrosion protection and a long service life for the whole blade