MALLORY Mallory Sonalert Products Inc.	Part #	PB-1220PQ
Sales Outline Drawing	Revision	D

May not be suitable for all Medical and Aerospace applications. Contact Mallory Sonalert to discuss your application. NO CIRCUITRY

Oscillation Frequency (Hz)	2048	
Operating Voltage (Vp-p)	1.25 ~ 2.5	
Rated Voltage (Vp-p)	1.5	
Current Consumption Max. (mA)	40 at Rated Voltage	
Sound Pressure Level (dB/min)	85 at 10cm at Rated Voltage	
Coil Resistance (Ω)	16 ± 2	
Operating Temperature (°C)	-20 ~ +70	
Storage Temperature (°C)	-30 ~ +80	
Lead Pin	Tin Plated Brass	
Housing	PPO plastic resin (Color: Black)	
Weight (Grams)	1.4	
Condition by wave soldering (°C)	260 ± 5 / within 5 sec	
Condition by hand soldering (°C)	350 ± 20 / within 5 sec	
Options	For other options contact factory	

Dimensions: (units: mm)

ROHS Compliant

