



PART NUMBER	ITEM ① DB25	ITEM ② CABLE	ITEM ③ DB25	ITEM ④ SCREW	ITEM ⑤ CONTACT
SEE TABLE I	MALEMO LDED	NOTE 1	FEMALEM OLDED	4-40 THREAD MOLDED	GOLD PLATED 2-3 MICRONS

DRAWING NO. 30-9506MF(SEE TABLE I)					
REVISIONS					
01	OFFICIAL RELEASE				2009.09
	08-05-09	Y	Y	T	08 09:08:16 +08'00



受控 CONTROLLED DOCUMENT

编号 P/N	30-95XXMF	版本 Rev	01	日期 Rel'd Date	SEP 14,09
-----------	-----------	-----------	----	------------------	-----------



- NOTES:**
- CABLE: 25 CONDUCTORS,PVC JACKET CABLE,28 AWG,DRAIN WIRE, FOIL SHIELD, NON-UL TYPE, BEIGE COLOR JACKET.
 - ELECTRICAL SPECIFICATIONS
CURRENT RATING: 5 AMPS
INSULATOR RESISTANCE: 100KOHMS
 - PRODUCT SHOULD BE RoHS COMPLIANCE.
 - PACKAGING REQUIREMENT FOLLOWS ENGINEER DOCUMENT P/N 836-40200001XX

TABLE I

PART NUMBER	DESCRIPTION	LENGTH (FEET)	TOLERANCE (INCHES)
30-9506MF	D-25M TO D-25 FM 25 COND.6FT	6	±1.00
30-9510MF	D-25M TO D-25 FM 25 COND,10FT	10	±1.00
30-9525MF	D-25M TO D-25 FM 25 COND,25FT	25	±2.00

THIS DRAWING TO BE INTERPRETED PER ANSI Y 14.5M - 1994

COMPANY CONFIDENTIAL

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY BETTY.YU		DATE 08-05-09	
DECIMALS	mm	CHECKED BY BETTY.YU		DATE 08-05-09	
X	+ 0.5	APPROVED BY THOMAS		DATE 08-05-09	
X.X	+ 0.2				
X.XX	+ 0.1				
ANGLES	+ 0.5°	U/M	mm	Ⓢ	
THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.					
SHEET 1 OF 1		DRAWING NO. 30-9506MF (SEE TABLE I)		SIZE C	



Connectivity Solutions

TITLE
D-25M TO D-25FM 25 COND,XXFT
(SEE TABLE I)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[30-9510MF](#)