

**Sales Outline Drawing**Revision **C**

**May not be suitable for all Medical and Aerospace applications.  
Contact Mallory Sonalert to discuss your application.**

|                                  |  |
|----------------------------------|--|
| Oscillation Frequency (Hz)       | 3000 ± 500                                     |
| Operating Voltage (Vdc)          | 1.5 ~ 30                                       |
| Rated Voltage (Vdc)              | 12   |
| Current Consumption (mA/max)     | 12 at Rated Voltage                            |
| Sound Pressure Level (dB/min)    | 80 at 30cm at Rated Voltage                    |
| Tone/Pulse Rate (Hz)             | Constant                                       |
| Operating Temperature (°C)       | -20 ~ +70                                      |
| Storage Temperature (°C)         | -30 ~ +80                                      |
| Housing                          | ABS 777 UL94HB plastic resin<br>(Color: Black) |
| Lead Wires                       | 28 AWG   |
| Weight (Grams)                   | 3.2  |
| Condition by wave soldering (°C) | 245 ±5 / 3±0.5 sec                             |
| Condition by hand soldering (°C) | 350 ±20 / within 5 sec                         |
| Options                          | For other options contact factory              |

**RoHS Compliant****Dimensions:** (units: mm)