

# PRODUCT DATASHEET

## P PIN 20 1.8 W/2700 G4

PARATHOM LED PIN G4 12 V | Low-voltage 12 V LED lamps with retrofit pin base G4



---

### AREAS OF APPLICATION

- Atmospheric accent lighting throughout the home
- Shops, hotels and restaurants
- Foyers, offices
- Outdoor applications only in suitable luminaires

---

### PRODUCT BENEFITS

- Long lifetime of up to 15,000 h
- Low energy consumption
- Ideal for decorative and free-burning applications

---

### PRODUCT FEATURES

- LED alternative to conventional low voltage lamps
- Mercury-free lamps



## TECHNICAL DATA

### Electrical data

Rated wattage	1.80 W
Nominal wattage	1.80 W
Nominal voltage	12 V
Power factor $\lambda$	0.50
Claimed equiv. conventional lamp power	20 W


### Photometrical data

Nominal luminous flux	200 lm
Rated luminous flux	200 lm
Rated color temperature	2700 K
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 K
Luminous flux	200 lm
Color rendering index Ra	$\geq 80$
Standard deviation of color matching	$\leq 6$ sdc <sub>m</sub>
Color rendering index Ra	$\geq 80$

### Light technical data

Warm-up time (60 %)	< 0.50 s
Beam angle	300.00 °
Starting time	< 0.5 s

### Dimensions & weight



Overall length	36.0 mm
Diameter	14.0 mm
Outer bulb	T14

<b>Length</b>	36.0 mm
---------------	---------

### Temperatures & operating conditions

<b>Maximum temperature at tc test point</b>	88 °C
---	-------

### Lifespan

<b>Nominal lamp life time</b>	15000 h
<b>Rated lamp life time</b>	15000 h
<b>Number of switching cycles</b>	100000
<b>Lumen maintenance at end of service life</b>	0.70

### Additional product data

<b>Base (standard designation)</b>	G4
<b>Mercury content</b>	0.0 mg
<b>Mercury-free</b>	Yes
<b>Design / version</b>	Clear
<b>Show WEEE picto</b>	Yes

### Capabilities

<b>Dimmable</b>	No
-----------------	----

### Certificates & standards

<b>Energy efficiency class</b>	A++
<b>Energy efficiency class</b>	A++
<b>Energy consumption</b>	2 kWh/1000h

### Country-specific categorizations

<b>ILCOS</b>	DRT/C-1,8/827-220-240-G4-14/36
<b>Order reference</b>	LEDPPIN20 CL 1,

## LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075811430	P PIN 20 1.8 W/2700 G4	Shipping carton box 20	150 mm x 122 mm x 77 mm	1.41 dm <sup>3</sup>	173.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## REFERENCES / LINKS

For further products and actual information concerning LED lamps see

▶ [www.ledvance.com/ledlamps](http://www.ledvance.com/ledlamps)

For Guarantee see

▶ [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

---

**DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.