
Item no.: 2016-1304
Product description: 3-Conductor through terminal block suitable for Ex e applications suitable for Ex i applications



Produkt kann von Bild abweichen / product may differ

Packing unit 20 pieces

RoHS compliant

| | |
|----------------------------------|--|
| Current intensity EN | 90 A |
| Product group | 22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS) |
| Cross section [mm ²] | 0.5 - 16 mm ² |
| Cross section [AWG] | 20 - 4 AWG |
| Connection method | CAGE CLAMP®S Connection |
| Cross section [mm ²] | 0.5 - 25 mm ² |
| Cross section [AWG] | 20 - 4 AWG |
| Wiring method | f |
| Connection method | CAGE CLAMP®S Connection |
| Measured voltage EN | 800 V |
| Measured shock voltage | 8 kV |
| Pollution degree | 3 |
| Current intensity EN | 76 A |
| Rated voltage EN (Ex e II) | 550 V |
| Nominal current (Ex e II) | 67 A |
| Weight | 26.712 g |
| Color | blue |
| Wiring type | Front-entry |

| | |
|--------------------------|----------|
| No. of connection Points | 3 |
| No. of potentials | 1 |
| Height | 37 mm |
| Height | 1.457 in |



| | |
|--------------------|-------------|
| Width | 12 mm |
| Width | 0.472 in |
| Depth | 92 mm |
| Depth | 3.622 in |
| Strip length from | 18 mm |
| Strip length to | 20 mm |
| Strip length | 0.75 in |
| Customs Tariff No. | 85369010 |
| Country of Origin | Deutschland |
| Mounting | TS 35 |



| Item number | Admission office | Approval no. | Voltage [V] | Current [A] | Cross section [mm ²] |
|-------------|------------------|-------------------|-------------|-------------|-----------------------------------|
| 2016-1304 | ABS | 05-HG476175/3-PDA | 800 | 76 | 0,5-25 |
| 2016-1304 | AEX | E185892 | 550 | 85 | 20-4 |
| 2016-1304 | CCA | NL6426 | 800 | 76/90 | 0,5-16 |
| 2016-1304 | CSA | 154112-1579112 | 600 | 85 | 20-4 |
| 2016-1304 | DNV | E-10423 | 800 | 76 | 0,5-25 |
| 2016-1304 | GL | 26187-05HH | 800 | 76 | 0,5-16 |
| 2016-1304 | KEMA | 2121287.03 | 800 | 76/90 | 0,5-25 |
| 2016-1304 | LR | 91/20112(E6) | 800 | 76 | 0,5-25 |
| 2016-1304 | PRS | TE/1718/880590/08 | 800 | 76 | 0,5-25 |
| 2016-1304 | PTB | IECEXPTB05.0015U | 550 | 33 | 0,5-25(25 ² hur |
| 2016-1304 | PTB | PTB05Atex1031U | 550 | 33 | 0,5-25(25 ² hur |
| 2016-1304 | RosTest | 8189158 | 550 | 33 | 0,5-25(25 ² hur |
| 2016-1304 | UR | E45172 | 600 | 85 | 20-4 |

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected