

Between Series Adaptor

33_BNC-A-0-1/0--_-

Description

Adaptor plug/jack
BNC plug (male) / A jack (female)

Interface standards
Series BNC - IEC 61169-8_MIL-STD-348A/301_CECC 22120
Series A - SUHNER-A



Technical Data

Electrical Data

Impedance other Ω
Interface frequency max. 4 GHz

Mechanical Data

Number of matings 500
Weight 0.0192 kg

Environmental Data

Operating temperature -20 °C to 85 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Interface - BNC plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - A jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Bronze	
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00014399

Ordering Information

Single package 33_BNC-A-0-1/0--_E