EAO – Your Expert Partner for **Human Machine Interfaces**

44-800.2 - Lever switch complete

44-800.2 - Lever switch complete



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Front

Front shape round Front dimension Ø 22 mm

Other Attributes

Weight 0,080 kg

Operating-/Indication part

Lever colour black Lever material Plastic

IP-Rating

Front protection IP65

Connection Method

Terminal Solder 2.8 x 0.5 mm

Actuator

Switching action Momentary

Switching element

Switching voltage 250 V AC Switching current 5 A

Contacts 2 NC + 2 NO

Switching system Snap-action switching element Contact material

Function


Lever switch

e a o


EAO – Your Expert Partner for **Human Machine Interfaces**

44-800.2 - Lever switch complete


Dimensions




Mounting cut-outs



Wiring diagram



Component layout



Additional information

2 positions (L-R)

With flat receptacle, VDE 0630 (SEV) specify use of insulating sleeve Part No. 280-0010-00

Legend

Contacts: NC = Normally closed, NO = Normally open Switching action: B = Momentary