

2399.0

H 1,0/12 YE



Wire-end ferrules, Max. wire cross-section: 1 mm<sup>2</sup>, Length: 12 mm, Length of copper pipe: 6 mm, Colour: Yellow

**RAL:** 1026

## Business data

Packaging unit	500
Quantity unit	PC
Weight per piece (not including packaging)	0.08 g
Weight per piece (including packaging)	0.09 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules

2399.0

H 1,0/12 YE

---

## Technical data

---

### Dimensions

---

Length	12 mm
Length of copper pipe	6 mm
Diameter of copper pipe	1.4 mm
Diameter plastic collar	3 mm
Wall thickness of copper pipe	0.15 mm
Wall thickness of plastic collar	0.25 mm

### Connection data

---

Wire cross-section, max.	1 mm <sup>2</sup>
Wire cross-section AWG, max.	17
Stripping length	8 mm

### Materials

---

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

### Further technical data

---

Insulation available	✓
----------------------	---

### Print

---

Colour	Yellow
--------	--------

### Environmental Product Compliance

---

REACH Conform	yes
REACH Reference date	2021-01-09, 2021-07-08
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet



2399.0

H 1,0/12 YE

---

## Approvals

---

### Standards and regulations

---

DIN 46228-4:1990	yes
------------------	-----

---

# Data sheet

2399.0

H 1,0/12 YE



---

## Accessories

---