

## Han 16A/25EMV-AK f. Easy-Lock



Part number	09 20 016 5425
Specification	Han 16A/25EMV-AK f. Easy-Lock
HARTING eCatalogue	<a href="https://b2b.harting.com/09200165425">https://b2b.harting.com/09200165425</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A <sup>®</sup>
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings
	for surface mounted housings
	for cable to cable housing
	Metal
	With fixing cord
Type	Low construction
	High construction

### Version

Locking type	Single locking lever
Size	16 A
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

Surface (hood/housing)	Powder-coated
Material (seal)	NBR



Pushing Performance

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	56.54 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors