

## FEATURES

- IP67 Rated
- Voltage ratings of 415V and 230v offered in this range
- All models offered in the range are highly reliable and excellent quality
- Right angle body orientation
- Maximum operating temperature of 40 °C
- Ample room for wiring the switch-disconnector mechanical interlock that can be fitted with auxiliary contact
- Lockable control knob and threaded metal inserts

## RS PRO IP67 Red Panel Mount 3P+N+E Right Angle Industrial Power Socket, Rated At 63.0A, 415.0 V

RS Stock No.: 780-0775



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

From RS PRO, comes a range of high-quality panel mounted power connectors. Manufactured to industry standards these red connectors are easy to assemble and is a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements

## General Specifications

<b>Syntetical Description</b>	Interlocked Socket
<b>Pole Format</b>	3P+N+E
<b>Hour Position</b>	6h
<b>Gender</b>	Female
<b>Body Orientation</b>	Right Angle
<b>Colour</b>	Red
<b>Locking Mechanism</b>	Control knob
<b>Applications</b>	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

## Electrical Specifications

<b>Type of Current</b>	AC
<b>Current Rating</b>	63A
<b>Voltage Rating</b>	415V
<b>Working Frequency</b>	50Hz; 60Hz
<b>Plug/Socket</b>	Socket

## Mechanical Specifications

<b>Mounting Type</b>	Panel Mount
----------------------	-------------

## Operation Environment Specifications

Maximum Operating Temperature	40°C
Minimum Operating Temperature	-25°C

## Protection Category

IP Rating	IP67
-----------	------

## Approvals

Compliance/Certifications	EN61340
---------------------------	---------

