



Description: 0.283" Right Angle / Machined

Dimensions (inch/mm)

Pins	A	B	C	D	E	F
9	1.213	0.984	0.665	0.327	0.240	0.492
	30.80	25.00	16.90	8.30	6.10	12.50
15	1.543	1.311	0.994	0.327	0.240	0.492
	39.20	33.30	25.25	8.30	6.10	12.50
25	2.089	1.852	1.533	0.327	0.240	0.492
	53.05	47.05	38.95	8.30	6.10	12.50
37	2.732	2.500	2.181	0.327	0.240	0.492
	69.40	63.50	55.40	8.30	6.10	12.50
50	2.638	2.402	2.079	0.429	0.236	0.602
	67.00	61.00	52.80	10.90	6.00	15.30



Material:

Shell: Nickel Plated Steel
 Insulator: UL 94V-O Rated, White PA6T
 Process Temperature: 260°C
 Contact: Precision Machined Copper Alloy

Electrical:

Current Rating: 5 AMPS
 Contact Resistance: 10 mOhms Max.
 Insulation Resistance: 5 GOhms Min.
 Working Voltage: 250V
 Temperature: -55° C TO +125° C

173-EYY-11YRYY1

Series
Position
 E09
 E15
 E25
 E37
 E50
Gender
 1 = Male
Termination
 1 = PCB Mounting
Shell Plating
 3 = Nickel
RoHS Compliant
Hardware Options
 00 = No Hardware
 0A = 0.098" Clinch Nut (Board Side)
 14 = Standard Bracket with 4-40 Screwlock
 24 = Standard Bracket with 4-40 Captive Screw
 46 = Boardlock Bracket with 4-40 Insert
Plating Options
 1 = Gold Flash
 2 = 30µ" Gold
 3 = 50µ" Gold

RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING




THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
 PAM JENKINS
 DATE:
 11/28/2005


NorComp

SCALE: NTS
 SHEET 1 OF 3
 REV 23
 DWG NO. 173-EYY-11YRYY1


9 POSITION




15 POSITION




25 POSITION



37 POSITION



50 POSITION



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING




THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS
DATE:
11/28/2005

NorComp


SCALE: NTS	SHEET 2	OF 3	REV 23
DWG NO.		173-EYY-11YRY1	

0A Hardware Option
0.098" Clinch Nut (Board Side)




Clinch Nut has 4-40 Internal Threads

14 Hardware Option		
	Description	NorComp Part Number
1	4-40 Screwlock	SFSO4401NR
2	Bracket	K501CZ
3	Lock Washer	LW1-T
4	4-40 Nut	N4401N



**Search Hardware Part Number To Obtain Technical Specifications.


24 Hardware Option		
	Description	NorComp Part Number
1	4-40 Captive Screw	SSH4401T
2	Bracket	K501CZ
3	Lock Washer	LW1-T
4	4-40 Nut	N4401N




**Search Hardware Part Number To Obtain Technical Specifications.

46 Hardware Option
Boardlock Bracket and 4-40 Insert

#4-40 Threaded Insert




9-37 Position Connector Boardlock Bracket



Hole C/L
0.339 [8.62]

50 Position Connector Boardlock Bracket
** 50 Position Comes With Locator Plate



Hole C/L
0.395 [10.03]

Boardlock Brackets Come Assembled On Connector

RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS
DATE:
11/28/2005

NorComp

SCALE: NTS	SHEET 3	OF 3	REV 23
DWG NO.		173-EYY-11YRY1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[173-E50-113R141](#) [173-E09-113R001](#) [173-E15-113R001](#) [173-E25-113R001](#) [173-E37-113R001](#) [173-E37-113R141](#)
[173-E50-113R001](#) [173-E09-113R141](#) [173-E25-113R141](#) [173-E15-113R141](#) [173-E25-113R241](#) [173-E50-113R241](#)
[173-E09-113R461](#) [173-E15-113R461](#) [173-E25-113R461](#) [173-E37-113R461](#) [173-E50-113R461](#)