

## Specification Sheet

Part Number: FU16-M20-M



Nickel plated brass compression fitting used with FU-x series flexible metallic conduit.

Two part fitting comprised of shell and body with external metric thread delivers IP40 ingress protection.

Suitable for knockouts and secured with a metric threaded locknut.

Metallic Compression Fitting, Fixed Straight, M20 Metric Thread, 3/8" (16mm) Dia, NPB Metal, 10/pkg

**Article Number** 166-90763

**Type** FU16-M20-M

**Color** Metal (ML)

**Quantity Per** pack

**Product Description** Two-part nickel plated brass straight fitting with fixed external metric thread. Fitting comprised of shell and body suitable for knockout entries. For use with FU-x flexible metal conduit.

**Short Description** Metallic Compression Fitting, Fixed Straight, M20 Metric Thread, 3/8" (16mm) Dia, NPB Metal, 10/pkg

**Global Part Name** FU16-M20-M-NPB-ML

**Technical Description** Manufacturer Reference Number: FU16-M20-M

**Length L (Imperial)** 0.98

**Length L (Metric)** 25.0

**Variant** Straight

**Height H (Imperial)** 0.87

**Height H (Metric)** 22.0

**Nominal Diameter (Imperial)** 0.38

**Nominal Diameter (Metric)** 16.0

**Material** Nickel Plated Brass (NPB)

**Material Shortcut** NPB

**Halogen Free** Yes

**Operating Temperature** -58°F to +572°F (-50°C to +300°C)

**Reach Compliant (Article 33)** Yes

**ROHS Compliant** Yes

**Package Quantity (Imperial)** 10

**Package Quantity (Metric)** 10

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FU16-M20-M](#)