

BU508AF

High voltage NPN power transistor for standard definition CRT display

Features

- State-of-the-art technology:
 - Diffused collector "Enhanced generation"
- Stable performances versus operating temperature variation
- Low base-drive requirement
- Tight h_{FE} range at operating collector current
- High ruggedness
- Fully insulated power package U.L. compliant

Applications

- Horizontal deflection output for CRT TV
- Switch mode power supplies for CRT TV



The BU508AF is manufactured using diffused collector in planar technology adopting new and enhanced high voltage structure for updated performance to the horizontal deflection stage.




Figure 1. Internal schematic diagram




Table 1. Device summary

Order code	Marking	Package	Packaging
BU508AF	BU508AF	ISOWATT218FX	Tube

Content BU508AF

Content

1	Elec	rical ratings
2	Elec	trical characteristics
	2.1	Electrical characteristics (curves)
	2.2	Test circuits
3	Pack	age mechanical data
4	Revi	sion history 1(

BU508AF Electrical ratings

1 Electrical ratings

Table 2. Absolute maximum rating

Symbol	Parameter	Value	Unit
V _{CES}	Collector-emitter voltage (V _{BE} = 0)	1500	V
V _{CEO}	Collector-emitter voltage (I _B = 0)	700	V
V _{EBO}	Collector-base voltage (I _C = 0)	9	V
I _C	Collector current	8	Α
I _{CM}	Collector peak current (t _P < 5ms)	15	Α
I _B	Base current	4	Α
P _{TOT}	Total dissipation at T _c = 25°C	50	W
V _{ins}	V _{ins} Insulation withstand voltage (RMS) from all three leads to external heatsink		V
T _{stg}	Storage temperature	-65 to 150	°C
T _J	Max. operating junction temperature	150	

Table 3. Thermal data

Symbol	Parameter	Value	Unit
R _{thj-case}	Thermal resistance junction-case max	2.5	°C/W

5/

Electrical characteristics BU508AF

2 Electrical characteristics

 $(T_{case} = 25^{\circ}C \text{ unless otherwise specified})$

Table 4. Electrical characteristics


Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
I _{CES}	Collector cut-off current (V _{BE} =0)	V _{CE} = 1500V V _{CE} = 1500V; T _C = 125°C	;		0.2 2	mA mA
I _{EBO}	Emitter cut-off current (I _C =0)	V _{EB} = 9V			1	mA
V _{CEO(sus)} (1)	Collector-emitter sustaining voltage (I _C =0)	I _C = 100mA	700			V
V _{CE(sat)} (1)	Collector-emitter saturation voltage	$I_C = 4.5A$ $I_B = 1.6A$	١		1	V
V _{BE(sat)} (1)	Base-emitter saturation voltage	$I_C = 4.5A$ $I_B = 2A$	١		1.1	V
h _{FE} ⁽¹⁾	DC current gain	$I_C = 0.1A$ $V_{CE} = 5$ $I_C = 4.5A$ $V_{CE} = 5$			30	
t _s	Inductive load Storage time Fall time	$I_{C} = 4.5 A$ $I_{B(on)} = 0.5 A$ $V_{BE(off)} = -2.7 V$ $f_{h} = 16 KHz$ $L_{BB(off)} = 4.5 \mu H$		2.5 0.2		μs μs

^{1.} Pulsed: Pulse duration = 300 ms, duty cycle 1.5 %

2.1 Electrical characteristics (curves)

Figure 2. Safe operating area

Figure 3. Derating curve







Figure 4. DC current gain

Figure 5. DC current gain








Figure 6. Collector-emitter saturation voltage

Figure 7. Base-emitter saturation voltage






577

Electrical characteristics BU508AF

Figure 8. Output characteristics



2.2 Test circuits

Figure 9. Power losses and inductive load switching





Figure 10. Reverse biased safe operating area




577

3 Package mechanical data

In order to meet environmental requirements, ST offers these devices in ECOPACK® packages. These packages have a Lead-free second level interconnect. The category of second level interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97. The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark. ECOPACK specifications are available at: www.st.com

ISOWATT218FX mechanical data

Dim.	mm.				
Dilli.	Min. Typ		Max.		
А	5.30		5.70		
С	2.80		3.20		
D	3.10		3.50		
D1	1.80		2.20		
E	0.80		1.10		
F	0.65		0.95		
F2	1.80		2.20		
G	10.30		11.50		
G1		5.45			
Н	15.30		15.70		
L	9		10.20		
L2	22.80		23.20		
L3	26.30		26.70		
L4	43.20		44.40		
L5	4.30		4.70		
L6	24.30		24.70		
L7	14.60		15		
N	1.80		2.20		
R	3.80		4.20		
Dia	3.40		3.80		



577

Revision history BU508AF

4 Revision history

Table 5. Document revision history

Date	Revision	Changes
02-Mar-2007	1	Initial release
14-Aug-2007	2	Complete document, added all curves (2.1: Electrical characteristics (curves)

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2007 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics: BU508AF