

Han B Hood Side Entry HC 2 Reels PG 21



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 024 0540
Specification	Han B Hood Side Entry HC 2 Reels PG 21
HARTING eCatalogue	https://b2b.harting.com/09300240540

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Hood
Type	High construction

Version

Size	24 B
Version	Side entry
Cable entry	1x Pg 21
Locking type	Single locking lever
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
	IP66
	IP67
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated



Pushing Performance

Material properties

Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

Commercial data

Packaging size	1
Net weight	250 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09300240540](#)