


CRZ 1362

ROHS COMPLIANT




Har-Flex female 32pole, with Strain relief, PL2

C1

Har-Flex 32P female connector

C2

Har-Flex 32P female connector



Part-No./产品号码	Length/长度
33 15 243 050 0012 .00	500±5
33 15 243 020 0011 .00	200±3
33 15 243 010 0010 .00	100±3

Ref: MB  
Mat: SEE BILL OF MATERIAL

- NOTES/要求:
- 1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST AND HI-POT (300VDC) TEST.
  - 2.) CABLE OPERATION TEMPERATURE=-30° C TO +105° C.
  - 3.) WHITE LABEL CONTENT:

DATE CODE & LOT INFORMATION  
HARTING P/N & REVISION

Rev.	Description	Appr.	Date
01	Add side view.	Lucy.Z	15/04/13
00	Prototype	Andr-ew.H	24/05/11

Free size tol.		All Dimensions in mm Original Size DIN A4	
V=	cm <sup>3</sup>	A=	cm <sup>2</sup>
Detail	Name	Date	Scale
Insp.			Sheet
Approved			1 of 1

HARTING (Zhuohai) Manufacturing Co., Ltd	HARTING	DWG. No. TB_33 15 0004 .01
--	---------	----------------------------

4

3

2

1

A

B

C

D

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33152430200011](#) [33152430500012](#) [33152430100010](#)