

A range of lightweight professional shovels designed to reduce the risk of personal injury when working near live cables.



The Fibrelite shaft is not only lightweight and extremely strong, but also fire and water resistant. The shorter socket length makes it easier to avoid touching metal whilst in use, thereby increasing safety



One piece heads forged from manganese steel for maximum strength

Round bar treaded heads for more comfortable digging

Heat treated and tempered to give quality, performance and long life

Rounded corners reduce the risk of damage to pipes and cables

CONTRACTORS TOOLS

fibrelite range

square mouth

2731TFL



Handle Type: MYD
 Socket Size: 190mm (7½")
 Blade Size: 302mm (12") x 250mm (10")
 Handle Length: 711mm (28")

trenching shovel

2701TFL



Handle Type: MYD
 Socket Size: 190mm (7½")
 Blade Size: 276mm (11") x 172mm (7")
 Handle Length: 711mm (28")

round mouth

2721TFL



Handle Type: MYD
 Socket Size: 190mm (7½")
 Blade Size: 305mm (12¼") x 240mm (9½")
 Handle Length: 711mm (28")

taper mouth

2702TFL



Handle Type: MYD
 Socket Size: 190mm (7½")
 Blade Size: 315mm (12½") x 218mm (8¾")
 Handle Length: 711mm (28")

cube layer

2711TFL



Handle Type: MYD
 Socket Size: 190mm (7½")
 Blade Size: 276mm (11") x 119mm (4¾")
 Handle Length: 711mm (28")

newcastle drainer

2753TFL



Handle Type: MYD
 Socket Size: 190mm (7½")
 Blade Size: 405mm (16¼") x 105mm (4")
 Handle Length: 711mm (28")

trenching fork

2741TFL



Handle Type: MYD
 Socket Size: 190mm (7½")
 Head Size: 325mm (13") x 215mm (8½")
 Handle Length: 711mm (28")

