



Part Number : [398800302](#)

Product Description : 5.08mm Pitch, Beau Eurostyle Low Profile, Fixed Block, Modular, 2 Circuits

Series Number : 39880

Status : Active

Product Category : Terminal Blocks and Barrier Strip

Engineering Number : MX-MSB02005-0N



Documents & Resources

Drawings


[Drawing 398800302_sd.pdf](#)

3D Models and Design Files

[3D Model 398800302_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39880
Description	5.08mm Pitch, Beau Eurostyle Low Profile, Fixed Block, Modular, 2 Circuits
Application	N/A
Component Type	One Piece
Product Family	Eurostyle Terminal Blocks
Product Name	Eurostyle Fixed Mount
Type	Euro Block
UPC	800753319059

Agency

UL	E167473
----	---------

Electrical

Current - Maximum per Contact	13.5A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	2
Entry Angle	Horizontal
Flammability	94V-0
Lock to Mating Part	None
Net Weight	1.750/g
Number of Rows	1
Orientation	Vertical

Panel Mount	No
PC Tail Length	3.50mm
PCB Retention	None
PCB Thickness - Recommended	2.40mm
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	N/A
Shrouded	Fully
Stackable	Yes
Temperature Range - Operating	105°C
Wire Size (AWG)	16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm ²	0.20-1.50

This document was generated on Dec 09, 2023