

## Han 10B-kg-LB-M20



|                    |   |
|--------------------|---|
| Part number        | 19 30 010 1750  |
| Specification      | Han 10B-kg-LB-M20   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19300101750">https://b2b.harting.com/19300101750</a> |

### Identification

|                          |                        |
|--------------------------|------------------------|
| Category                 | Hoods/Housings         |
| Series of hoods/housings | Han <sup>®</sup> B     |
| Type of hood/housing     | Cable to cable housing |
| Type                     | Low construction       |

### Version

|                            |   |
|----------------------------|---|
| Locking type               | Single locking lever                              |
| Han-Easy Lock <sup>®</sup> | Yes   |
| Size                       | 10 B  |
| Version                    | Top entry   |
| Cable entry                | 1x M20  |
| Field of application       | Standard hoods/housings for industrial connectors |

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65            |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12   |

### Material properties

|                         |                      |
|-------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast   |
| Surface (hood/housing)  | Powder-coated        |
| Colour (hood/housing)   | RAL 7037 (dust grey) |



Pushing Performance

## Material properties

|  |                                  |
|--|----------------------------------|
| Material (seal)  | NBR                              |
| Material (locking)   | Polycarbonate<br>Stainless steel |
| Colour (locking)   | RAL 7037 (dust grey)             |
| Material flammability class acc. to UL 94 (locking levers) | V-0                              |
| RoHS   | compliant                        |
| ELV status   | compliant                        |
| China RoHS   | e                                |
| REACH Annex XVII substances                                | No                               |
| REACH ANNEX XIV substances                                 | No                               |
| REACH SVHC substances                                      | No                               |

## Specifications and approvals

|           |  |
|-----------|--|
| Approvals | DNV GL   |
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 156.3 g                                  |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |