

**CDL4U(E)DD1/DD2**



Diode circuit for lamp testing

6 mm

54 x 55.5 mm

300 V~

9 mm

Polyamide 6.6

|           |             |              |
|-----------|-------------|--------------|
|           |             |              |
| C US      | 60947-7-1   | C US E220514 |
| 22-10 AWG | 0.2-4 sq.mm | 22-10 AWG    |
| 300 V     | 500 V       | 600 V        |
| 25 A      | 32 A        | 35 A         |
| 7 lb-in   | 0.5 Nm      | 7 lb-in      |



| Cat. No.           | Std. Pk. |
|--------------------|----------|
| <b>CDL4U(E)DD1</b> | 100      |
| <b>CDL4U(E)DD2</b> | 100      |
| EPCDL4U            | 50       |




|       |    |
|-------|----|
| CA702 | 50 |
| CA802 | 50 |

|          |     |
|----------|-----|
| CA727/2  | 100 |
| CA727/3  | 100 |
| CA727/4  | 100 |
| CA727/10 | 10  |


|            |     |
|------------|-----|
| CA703/1    | 100 |
| CA704/1    | 100 |
| CA705/1    | 100 |
| CA732/10   | 100 |
| CA732/10-A | 100 |
| CA732/100  | 10  |

|           |     |
|-----------|-----|
| CA607/S/Q | 100 |
|-----------|-----|

|     |     |
|-----|-----|
| MT2 | 100 |
|-----|-----|



DD1



DD2

**CDL4U(E)DD3/DD4**



Diode circuit for lamp testing

6 mm

54 x 55.5 mm

300 V~

9 mm

Polyamide 6.6

|           |             |              |
|-----------|-------------|--------------|
|           |             |              |
| C US      | 60947-7-1   | C US E220514 |
| 22-10 AWG | 0.2-4 sq.mm | 22-10 AWG    |
| 300 V     | 500 V       | 600 V        |
| 25 A      | 32 A        | 35 A         |
| 7 lb-in   | 0.5 Nm      | 7 lb-in      |



| Cat. No.           | Std. Pk. |
|--------------------|----------|
| <b>CDL4U(E)DD3</b> | 100      |
| <b>CDL4U(E)DD4</b> | 100      |
| EPCDL4U            | 50       |




|       |    |
|-------|----|
| CA702 | 50 |
| CA802 | 50 |

|          |     |
|----------|-----|
| CA727/2  | 100 |
| CA727/3  | 100 |
| CA727/4  | 100 |
| CA727/10 | 10  |


|            |     |
|------------|-----|
| CA703/1    | 100 |
| CA704/1    | 100 |
| CA705/1    | 100 |
| CA732/10   | 100 |
| CA732/10-A | 100 |
| CA732/100  | 10  |

|           |     |
|-----------|-----|
| CA607/S/Q | 100 |
|-----------|-----|

|     |     |
|-----|-----|
| MT2 | 100 |
|-----|-----|



DD3



DD4

**CDL4U(E)D4**



Diode circuit for lamp testing with LED series resistance

6 mm

54 x 55.5 mm

12V~/24 V~

9 mm

Polyamide 6.6

|           |             |              |
|-----------|-------------|--------------|
|           |             |              |
| C US      | 60947-7-1   | C US E220514 |
| 22-10 AWG | 0.2-4 sq.mm | 22-10 AWG    |
| 300 V     | 500 V       | 600 V        |
| 25 A      | 32 A        | 35 A         |
| 7 lb-in   | 0.5 Nm      | 7 lb-in      |



| Cat. No.          | Std. Pk. |
|-------------------|----------|
| <b>CDL4U(E)D4</b> | 100      |
| EPCDL4U           | 50       |




|       |    |
|-------|----|
| CA702 | 50 |
| CA802 | 50 |

|          |     |
|----------|-----|
| CA727/2  | 100 |
| CA727/3  | 100 |
| CA727/4  | 100 |
| CA727/10 | 10  |

|            |     |
|------------|-----|
| CA703/1    | 100 |
| CA704/1    | 100 |
| CA705/1    | 100 |
| CA732/10   | 100 |
| CA732/10-A | 100 |
| CA732/100  | 10  |


|           |     |
|-----------|-----|
| CA607/S/Q | 100 |
|-----------|-----|

|     |     |
|-----|-----|
| MT2 | 100 |
|-----|-----|



D4

**CDL4U(E)DD5**



Diode circuit for lamp testing with LED series resistance

6 mm

54 x 55.5 mm

12V~/24 V~

9 mm

Polyamide 6.6

|           |             |              |
|-----------|-------------|--------------|
|           |             |              |
| C US      | 60947-7-1   | C US E220514 |
| 22-10 AWG | 0.2-4 sq.mm | 22-10 AWG    |
| 300 V     | 500 V       | 600 V        |
| 25 A      | 32 A        | 35 A         |
| 7 lb-in   | 0.5 Nm      | 7 lb-in      |



| Cat. No.           | Std. Pk. |
|--------------------|----------|
| <b>CDL4U(E)DD5</b> | 100      |
| EPCDL4U            | 50       |




|       |    |
|-------|----|
| CA702 | 50 |
| CA802 | 50 |

|          |     |
|----------|-----|
| CA727/2  | 100 |
| CA727/3  | 100 |
| CA727/4  | 100 |
| CA727/10 | 10  |

|            |     |
|------------|-----|
| CA703/1    | 100 |
| CA704/1    | 100 |
| CA705/1    | 100 |
| CA732/10   | 100 |
| CA732/10-A | 100 |
| CA732/100  | 10  |

|           |     |
|-----------|-----|
| CA607/S/Q | 100 |
|-----------|-----|

|     |     |
|-----|-----|
| MT2 | 100 |
|-----|-----|



DD5

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CDL4U\(E\)DD3](#) [CDL4U\(E\)DD5](#) [CDL4U\(E\)DD1](#) [CDL4U\(E\)DD2](#) [CDL4U\(E\)DD4](#) [CDL4U\(E\)D4](#)