YF2A14-020VB3XLEAX



YF2A14-020VB3XLEAX



Ordering information

Туре	Part no.
YF2A14-020VB3XLEAX	2096234

Other models and accessories -> www.sick.com/



Detailed technical data

Technical specifications


Accessory group		Plug connectors and cables
Accessory family		Connecting cables
Connection type head A		Female connector, M12, 4-pin, straight, A-coded
Connection type head B		Flying leads
Locking plug connector		Screw connection
Connector material		TPU
Connector color		Black
Locking nut material		Zinc die-cast, nickel-plated
Seal material		FKM
Tightening torque		0.6 Nm
Width across flats		13
Cable		2 m, 4-wire, PVC
Jacket material		PVC
Jacket color		Gray
Cable diameter		5 mm
Conductor cross-section		0.34 mm ²
Shielding		Unshielded
Bending radius		
	Flexible use	> 10 x cable diameter
Sta	ationary position	> 5 x cable diameter
Reference voltage		≤ 250 V AC/DC
Rated impulse voltage		2.5 kV
Current loading		4 A
Signal type		Sensor/actuator cable
Application		Zones with chemicals
Authorizations		CE UL
UL File No.		E335179
Enclosure rating		IP65 / IP66K / IP67

Ambient operating temperature	
Flexible use	-5 °C +80 °C
Stationary position	-30 °C +80 °C
Head	-25 °C +85 °C
Contamination rating	3
Insulation resistance	100 ΜΩ
Overvoltage category	Ш
Specific insulation resistance	30 mΩ
Thermal resistance, cable	Flame retardant according to UL 1581 VW1 / CSA FT1

Classifications

ECI@ss 5.0	19030312
ECI@ss 5.1.4	19030312
ECI@ss 6.0	27060304
ECI@ss 6.2	27060304
ECI@ss 7.0	27060304
ECI@ss 8.0	27060304
ECI@ss 8.1	27060304
ECI@ss 9.0	27060304
ECI@ss 10.0	27060304
ECI@ss 11.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249
ETIM 8.0	EC003249
UNSPSC 16.0901	26121604

Dimensional drawing (Dimensions in mm (inch))



YF2A14-020VB3XLEAX

Recommended accessories

Other models and accessories → www.sick.com/

	Brief description	Туре	Part no.		
Other mounting accessories					
	1 piece, M12 mounting key set for SW13 with calibrated torque 0.6 Nm	TOOL-TW06M12AF13	5337208		
Plug connectors and cables					
	Head A: female connector, M12, 5-pin, straight Cable: unshielded	DOS-1205-G	6009719		
	Head A: male connector, M12, 5-pin, straight Cable: unshielded For field bus technology	STE-1205-G	6022083		

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

