


solenoid coil

VACF-B-C1-16B

Part number: 8030815

FESTO

Type C connection pattern, to EN 175 301, 120 V AC/60 Hz and 110 V AC/50-60 Hz



Data sheet

Feature	Value
Assembly position	Any
Duty cycle	100 %
Insulation class	H
Characteristic coil data	110/120 V AC: 50/60 Hz, pick-up power 4.4 VA, holding power 3.3 VA
Surge strength	2.5 kV
Degree of contamination	3
Permissible voltage fluctuation	+/- 10 %
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-20 ... 50 °C
Protection class	IP65
Ambient temperature	-20 ... 50 °C
Electrical connection	to EN 175301-803 Plug pattern type C to EN 175301-803
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material housing	PA Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper