

DC AXIAL FAN

JAMICON®

92X92X38 mm

KF0938-11 Series



- **Frame** : Plastic Material UL 94V-0
- **Impeller** : Plastic Material UL 94V-0
- **Speed Range** : ±10%

SPECIFICATIONS

Model	Bearing	Rated Voltage (V)	Operating Voltage (V)	Air Flow (CFM)	Static Pressure (inchH ₂ O)	Speed (R.P.M.)	Input Current (Amp)	Input Power (Watt)	Nominal Current (Amp)	Noise (dBA)	Weight (g)
KF0938B1UR	Dual Ball	12	10.2 ~ 13.8	153.07	0.99	6000	1.84	22.08	2.21	61.70	198
KF0938B1SR				121.01	0.66	4800	0.88	10.56	1.06	54.90	
KF0938B1HR				110.27	0.54	4400	0.70	8.40	0.84	52.90	
KF0938B1MR				97.15	0.41	3800	0.60	7.20	0.72	48.50	
KF0938B1LR				77.08	0.31	3200	0.43	5.16	0.52	43.30	
KF0938B1ER				61.60	0.20	2600	0.20	2.40	0.24	36.20	
KF0938B1VR				48.16	0.13	2000	0.13	1.56	0.16	31.40	
KF0938B2UR	Dual Ball	24	20.4 ~ 27.6	153.07	0.99	6000	0.88	21.12	1.06	61.70	
KF0938B2SR				121.01	0.66	4800	0.42	10.08	0.50	54.90	
KF0938B2HR				110.27	0.54	4400	0.36	8.64	0.43	52.90	
KF0938B2MR				97.15	0.41	3800	0.35	8.40	0.42	48.50	
KF0938B2LR				77.08	0.31	3200	0.22	5.28	0.26	43.30	
KF0938B2ER				61.60	0.20	2600	0.11	2.64	0.13	36.20	
KF0938B2VR				48.16	0.13	2000	0.07	1.68	0.08	31.40	
KF0938B4UR	Dual Ball	48	40.8 ~ 60.0	153.07	0.99	6000	0.48	23.04	0.58	61.70	
KF0938B4SR				121.01	0.66	4800	0.24	11.52	0.29	54.90	
KF0938B4HR				110.27	0.54	4400	0.20	9.60	0.24	52.90	
KF0938B4MR				97.15	0.41	3800	0.18	8.64	0.22	48.50	
KF0938B4LR				77.08	0.31	3200	0.15	7.20	0.18	43.30	
KF0938B4ER				61.60	0.20	2600	0.11	5.28	0.13	36.20	
KF0938B4VR				48.16	0.13	2000	0.07	3.36	0.08	31.40	

Specifications subject to change without notice

