



Model	TRI32N-B
Impedance	8, 16, 32 ohm
Nominal Power	0.5 w
Maximum Power	1 w
Resonance Frequency (Fo)	500 Hz
Response:	200~5KHz
S.P.L.:	93±2, 90±2, 86±2 dB
Height	4.6 mm