

## Datasheet

Item No. 92.238.3003.2

### Cable assembly GST18I3K1B- 25 30WS

Connection cable, female - free end, length 3m, GST18i3, 3 pole, 250 V, 20 A, cable type H05VV, cross section 2,5 mm<sup>2</sup>, colour of coding: white, colour of cable: white



Item No.	92.238.3003.2
EAN	4015573370371
order unit	20 Piece(s)

### Approvals



### Technical data

#### General

ArticlePrice	udp_no_price
Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	White
Color of housing inclusive strain relief	White

#### Model

Number of poles	3
Nominal cross section conductor	2.5 mm <sup>2</sup>
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	37 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H05VV-F
Cable colour	White
Cable diameter	10.2 mm
Version of cable	Female - free end

#### Material

Surface finish	Tin-plated
Halogen free	No

Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C
<b>Dimensions</b>	
Total length	3 m

Drawings