

## SVS ECO VALVE PLUG FORM C 8MM 230V



2+PE field-wireable M16x1.5

Form C (8 mm)  
250 V AC/DC  
without components  
metric  
field-wireable


Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

Illustration



Height: 26 mm



Product may differ from Image

**Form**

Form

30055

**Technical Data**

Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 6 A
Configuration	2 contacts + PE
Connection cross section	max. 0.5 mm <sup>2</sup>
Sealing range (cable Ø)	4...6 mm
Locking of ports	M2.5 (recommended torque 0.4 Nm)
Compression gland	M12×1.75 mm
Contact figure	Cable outlet can be turned in 90° steps
Protection	IP65 inserted and tightened (EN 60529)

**General data**

Temperature range	-40...+90 °C
Material (gasket)	NBR
Mounting method	inserted, tightened

**Commercial data**

country of origin	HU
customs tariff number	85366990
EAN	4048879187015
eClass	27279221
Packaging unit	1