




ENGLISH

# Datasheet

## Stock No. 1863089

### RS PRO Connector Assembly



M08 Female Straight

#### General Specification


Rated Operational Voltage	30 V
Current Rating	4A
Insulation Resistance	$\geq 100 \text{ M}\Omega$
Temperature Range	-25°C ... +75°C
Degree of Protection	IP67

#### Material Specification

Grip Material	Nylon 66
Contact	Cu-Zn
Contact Plating	Gold Plated
Contact Carrier	Nylon 66
O-Ring	Neoprene
Grip Colour	Black
Termination	Solderable Pin Type
Pole	4
Cable Gland	PG5
Coupling Nut	Brass Nickel-plated

All dimensions are in mm.

#### Pin Diagram



Specifications are subject to change without notice.



Type Approved  
Safety  
Regular Production  
Surveillance

www.tuv.com  
ID: 1111210482

