




0469 - DOUBLE FEMALE VENTED BSPP BALL VALVE



maximum working pressure	40 bar 4 MPa 580 psi
working temperature	-20 to 80 °C -4 to 176 °F 253 to 353 °K
body	NICKEL PLATED BRASS
retaining nut	NICKEL PLATED BRASS
stem	BRASS
stem seal	NBR
'O'-rings	NBR
ball seal	NBR
handle	ZAMAK

Part Nb

	C	E (mm)	F (mm)	F1 (mm)	H (mm)	H1 (mm)	L (mm)	L1 (mm)	M (mm)	ØT (mm)	 (kg)
	All	All	All	All	All	All	All	All	All	All	All
0469 04 10	G1/8	8	14	14	35	29	44	25	48	1.5	.092
0469 07 13	G1/4	12	24	24	46	43	59	31	70	2	.268
0469 10 17	G3/8	12	24	24	46	43	59	31	70	2	.246
0469 13 21	G1/2	15	27	27	47	44	67	34	70	2	.294
0469 18 27	G3/4	16.5	32	38	63	54	80	39	108	2.5	.668
0469 23 34	G1	19	41	46	67	57	94	47	108	3	1.026