
B UNLIMITED


		1		
Part Number:		DRAWN	10/20/2015	
SC250708-1	700 1	CJ	10/29/2015	
50230	7/00-1	CHECKED	11/17/2015	
		P.D	11/17/2015	
Description:	unamic Chaakar	APPROVED	11/17/2015	
nigh remp by	ynamic Speaker	J.S	11/17/2015	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Top View



Side View



Bottom View

16.00

Items	Specifications	Conditions					
Sound Pressure Level	96	dB (@ 10cm)					
Resonant Frequency	750	Hz	REVISION HISTORY				
Frequency Range	200 ~ 20,000	Hz	REV	DESCRIPTION	DATE	APPROVED	
Nominal Power	1	W		Released from Engineering	2/8/2014	J.S.	
Max. Power	1.3	W	1	New template, correct to show no wires	3/17/2017	C.E.	
Impedance	8	Ω	NOTES				
Cone Material	Cloth		1) All dimensions are in mm unless otherwise noted				
Mount Type	Frame Mount		2) All tolerances are ± 0.5 mm unless otherwise noted				
Storage Temperature	-40 ~ +85	℃	3) All parts meet RoHS				

4) Subject to change or redrawn without notice Operating Temperature -40 ~ +85 ۰C Weight 5