


**May not be suitable for all Medical and Aerospace applications.  
Contact Mallory Sonalert to discuss your application.**

**NO CIRCUITRY**

|                                  |                                     |
|----------------------------------|-------------------------------------|
| Oscillation Frequency (Hz)       | 2400 ± 250                          |
| Operating Voltage (Vp-p)         | 4.5 ~ 5.5                           |
| Rated Voltage (Vp-p)             | 5.0                                 |
| Current Consumption Max. (mA)    | 50 at Rated Voltage                 |
| Sound Pressure Level (dB/min)    | 85 at 10cm at Rated Voltage         |
| Coil Resistance (Ω)              | 45 ± 5                              |
| Operating Temperature (°C)       | -20 ~ +70                           |
| Storage Temperature (°C)         | -30 ~ +80                           |
| Lead Pin                         | Tin Plated Brass                    |
| Housing                          | PPO plastic resin<br>(Color: Black) |
| Weight (Grams)                   | 1.6                                 |
| Condition by wave soldering (°C) | 245 ± 5 / 3 ± 0.5 sec               |
| Condition by hand soldering (°C) | 350 ± 20 / within 5 sec             |
| Options                          | For other options contact factory   |

**Dimensions:** (units: mm)**ROHS Compliant****Packaging:**

Parts are supplied in tube (40 per tube).