




SIDE VIEW

BOTTOM VIEW







| Specifi | ications | | Notes | | Revision History | | | | | |
|----------------------------|--------------------|-------|-------------------------------|-------------------------------|---------------------------|-------------|------------|-----------|-------------|------|
| Description | Value | Unit | | | Version | Description | | Date | Approved | |
| Directivity | Unidirectional | | 1) All dimensions are in mm u | 1 | Released from Engineering | | | 2/9/2014 | J.S. | |
| Technology | Electret Condenser | | 2) All parts meet RoHS | | | | | | | |
| Sensitivity | -46 | (dB) | | | | | | | | |
| Frequency Range | 100 ~ 10,000 | (Hz) | | | | | | | | |
| Rated Voltage | 2 | (V) | | | | | | | | |
| Output Impedance | 2,200 | (Ohm) | | | | | | | | |
| Connection Method | Solder Pads | | | | | | | | | |
| Voltage Range | 1.0 ~ 10.0 | (V) | | | | | | | | |
| Max Rated Current | 0.5 | (mA) | | | Drawn by | Date | Checked by | Date | Approved by | Date |
| Min. Signal to Noise Ratio | >55 | (dB) | | | G.W. | 10/31/2013 | C.E. | 1/16/2014 | | |
| Operating Temperature | -10 ~ +50 | °C | Floativet Condensor Micro | | nhono | MU064602-1 | | | | |
| Storage Temperature | -20 ~ +60 | °C | DB UNLIMITED | Electret Condenser Microphone | | | | | | |