


TOP VIEW





BOTTOM VIEW



Specifica	ations	Notes		Revision History						
Description	Value	Unit	Notes		Version	Description		Date	Approved	
Directivity	Omnidirectional		1) All dimensions are in mm unless otherwise noted			Released from Engineering			10/21/2013	J.S
Technology	Electret Condenser		2) All parts meet RoHS							
Sensitivity	-25	(dB)								
Frequency Range	50 ~ 16,000	(Hz)								
Rated Voltage	4.5	(V)								
Output Impedance	2,200	(Ohm)								
Connection Method	Lead Wire and Connector									
Voltage Range	4.5 ~ 10	(V)		F						
Max Rated Current	0.5	(mA)			Drawn by	Date	Checked by	Date	Approved by	Date
Minimum Signal to Noise Ratio	>60	(dB)			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Operating Temperature	-20 ~ +60	°C		Electret Condenser Microphone		MO062504-1				
Storage Temperature	-25 ~ +70	°C	DB UNLIMITED							