

# KERN UIB600K-1

Pallet scale with steel load support (IP67) und the best price-to-performance ratio



## Measuring system

Adjustment options:	External calibration
Linearity:	200 g
Readability [d]:	200 g
Recommended adjusting weight:	500 kg (M2)
Repeatability:	200 g
Resolution:	3000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-600 kg
Warm up time:	10 min
Weighing capacity [Max]:	600 kg
Weighing system:	Strain gauge
Weighing units:	g kg lb oz

## Display

Display digit height:	2,500 cm
-----------------------	----------

## Functions

Data hold function:	yes
---------------------	-----

## Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

## Power supply

Battery:	4x1.5 V AA
Input voltage:	100 V - 240V AC 50/60Hz 0.3A
Mains adapter/adapter included:	EURO UK US

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time:	60 h
-----------------	------

## Service

Adjustment at the location of installation: 961-250

DAkkS Certificate:	963-130
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Pallet scale

## Packaging & shipping


Delivery:	48 h
Dimensions packaging (WxDxH):	1270 x 900 x 260 mm
Gross weight:	87 kg
Net weight:	51 kg
Shipping method:	Freight forwarder

## Construction

Cable length of display device:	5 m
Dimensions of display device (WxDxH):	235 x 115 x 52 mm
Dimensions of weighing plate (WxDxH):	1195 x 840 x 110 mm
Level indicator:	yes
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	1195 x 840 mm

## Piktogramme

### STANDARD



### OPTION

