

in/mm

	LxHxP	A	B	Window	I nom.	I max.
TR-10	1.02 x 1.73 x 1.10	-	-	10	25...63A	75.6A
iTR-10	26 x 44 x 28	-	-	-	-	-
TR-14	1.14 x 2.63 x 1.10	0.55	0.59	14	40...160A	192A
iTR-14	29 x 67 x 28	14	15	-	-	-
TR-21	1.45 x 2.56 x 1.69	0.82	0.90	21	63...250A	300A
iTR-21	37 x 65 x 43	21	23	-	-	-
TR-32	2.08 x 3.38 x 1.85	1.26	1.30	32 *	160...600A	720A
iTR-32	53 x 86 x 47	32	33	-	-	-

* \square max = 1.18 x 0.98 in / 30 x 25 mm
 \emptyset max = 1.26 in / 32 mm

