

## Specification Sheet

Part Number: 2P9C



Sheathing allows flexible routing and lead-out of cables.  
The inner edges are beveled preventing damage to cables.

Sheathing is reusable and resistant to most chemicals.

Spiralwrap is UL Recognized.

Spiralwrap Protective Sheathing, 0.25" Diameter, PTFE, Natural, 100 ft/roll

**Article Number** 161-05047

**Type** 2P

**Color** Natural (NA)

**Quantity Per** reel

**Product Description** HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize. Polytetrafluoroethylene-Teflon (PTFE) offers the widest operating temperature range of any material. It's chemically inert and nonflammable. Natural color is milky white. Available by special order in black and colors.

**Short Description** Spiralwrap Protective Sheathing, 0.25" Diameter, PTFE, Natural, 100 ft/roll

**Global Part Name** 2P-PTFE-NA

**Length L (Imperial)** 100.0

**Length L (Metric)** 30.48

**Variant** Spiral Binding

**Bundle Diameter Min (Imperial)** 0.18

**Bundle Diameter Min (Metric)** 4.75

**Bundle Diameter Max (Imperial)** 2.0

**Bundle Diameter Max (Metric)** 50.8

**Diameter D (Imperial)** 0.25

**Diameter D (Metric)** 6.35

**Nominal Diameter (Imperial)** 0.25

**Nominal Diameter (Metric)** 6.35

**Wall Thickness WT (Imperial)** .030

**Wall Thickness WT (Metric)** 0.76

<b>Material</b>	Polytetrafluoroethylene (PTFE)
<b>Material Shortcut</b>	PTFE
<b>Flammability</b>	Non-flammable
<b>Halogen Free</b>	No
<b>Operating Temperature</b>	-449°F to +500°F (-267°C to +260°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>UL Recognized (US)</b>	Yes
<b>Package Quantity (Imperial)</b>	100
<b>Package Quantity (Metric)</b>	30.48
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[2P9C](#)