

Vandal resistant switches



flush IP67

Panel cut-out 22.5 mm


- extremely robust and well designed
- solid stainless steel or aluminium with a choice of 8 colours
- vandal resistant front actuator
- extremely difficult to destroy
- faston terminals 2.8 x 0.5 mm

	stainless steel		neutral anodised aluminium **	
	body*	actuator*	body*	actuator*
1NC + 1NO	807 603 000		807 503 000	
2NC	807 604 000	867 604 000	807 504 000	867 504 000
2NO	807 605 000		807 505 000	

* Please order the body and the actuator at the same time; delivered factory fitted.

(Order example: body stainless steel/actuator neutral anodised aluminium, 807 603 000 + 867 504 000).



** Possible colour combination for aluminium anodised actuator and body: yellow, green, light blue, red, black, anthracite, gold, dark blue, orange.



weight 8.5/18 g

Accessories

Mounting spanner metal box spanner for fixation nut for fixation nut	M16 x 1 492 100 000 M22 x 1 492 105 000	
Anti-rotation ring limits the protection to IP40	060 661 000	
Faston pin 2.8 mm x 0.5 mm for wires 0.5 -1.0 mm ²	593 572 000	
Plug-in adapter solder terminals	893 550 000	
printed terminals max. load: 4A 48V AC/DC	893 551 000	
Insulating sleeve for faston pin	593 577 000	



* hole for anti-rotation device