



BF0910D



BF1810L



BF80C00



B11500



BF09T4D



BF00...

type	rated current (AC1)	(AC3)	kW rating (AC3) 400V	control	description	auxiliary contacts
Three-pole contactors (Ui 690V) / DC control circuit						
Permanent magnet types (Ui 690V) / DC control circuit (low consumption coil 5.4 watt)						
BF0910D...*	25A	9A	4.2kW	DC	3-pole contactor	1NO
BF1210D...*	28A	12A	5.7kW	DC	3-pole contactor	1NO
BF1810D...*	32A	18A	7.5kW	DC	3-pole contactor	1NO
BF2510D...*	32A	25A	12.5kW	DC	3-pole contactor	1NO
BF2600D...*	45A	26A	13.0kW	DC	3-pole contactor	-
BF3200D...*	56A	32A	16.0kW	DC	3-pole contactor	-
BF3800D...*	56A	38A	18.5kW	DC	3-pole contactor	-
Permanent magnet types (Ui 690V) / DC control circuit (extra-low consumption coil 2.4 watt)						
BF0910L□	25A	9A	4.2kW	DC	3-pole contactor	1NO
BF1210L□	28A	12A	5.7kW	DC	3-pole contactor	1NO
BF1810L□	32A	18A	7.5kW	DC	3-pole contactor	1NO
BF2510L□	32A	25A	12.5kW	DC	3-pole contactor	1NO
BF3200L□	56A	32A	16.0kW	DC	3-pole contactor	-
BF3800L□	56A	38A	18.5kW	DC	3-pole contactor	-
(Ui 1000V) / DC control circuit						
BF50C00...*	90A	50A	25kW	DC	3-pole contactor	-
BF65C00...*	110A	65A	33kW	DC	3-pole contactor	-
BF80C00...*	125A	80A	41kW	DC	3-pole contactor	-
BF95C00...*	125A	95A	50kW	DC	3-pole contactor	-
BF110C00...*	125A	110A	61kW	DC	3-pole contactor	-
(Ui 1000V) / AC/DC control circuit						
B11500...*	160A	110A	61kW	DC	3-pole contactor	-
B14500...*	250A	150A	80kW	DC	3-pole contactor	-
B18000...*	275A	185A	100kW	DC	3-pole contactor	-
B25000...*	350A	265A	140kW	DC	3-pole contactor	-
B31000...*	450A	320A	170kW	DC	3-pole contactor	-
B40000...*	550A	420A	225kW	DC	3-pole contactor	-
B50000...*	700A	520A	290kW	DC	3-pole contactor	-
B63000...*	800A	630A	335kW	DC	3-pole contactor	-
Four-pole contactors (Ui 690V) / DC control circuit						
type	rated current (AC1)		kW (AC1) 230V 400V	control	description	main contacts
Permanent magnet types (Ui 690V) - DC control circuit						
BF09T4D...*	25A	9.5	16	DC	4-pole contactor	4NO
BF18T4D...*	32A	12	21	DC	4-pole contactor	4NO
BF26T4D...*	45A	17	30	DC	4-pole contactor	4NO
BF38T4D...*	56A	21	36	DC	4-pole contactor	4NO
BF18T2D...*	32A	10	18	DC	4-pole contactor	2NO+2NC
BF26T2D...*	45A	12	21	DC	4-pole contactor	2NO+2NC
BF38T2D...*	56A	17	30	DC	4-pole contactor	2NO+2NC
BF18T0D...*	32A	10	18	DC	4-pole contactor	4NC
BF26T0D...*	45A	12	21	DC	4-pole contactor	4NC
(Ui 1000V) / AC/DC control circuit						
BF65C40...*	110A	41	72	DC	4-pole contactor	4NO
BF80C40...*	125A	47	82	DC	4-pole contactor	4NO
B115400	160A	57	98	DC	4-pole contactor	4NO
B145400	250A	91	150	DC	4-pole contactor	4NO
B180400	275A	95	160	DC	4-pole contactor	4NO
B250400	350A	124	214	DC	4-pole contactor	4NO
B310400	450A	158	270	DC	4-pole contactor	4NO
B400400	550A	200	345	DC	4-pole contactor	4NO
B500400	700A	252	438	DC	4-pole contactor	4NO
B630400	800A	288	500	DC	4-pole contactor	4NO
Control relays / DC control circuit (extra-low consumption coil 2.4 watt)						
BF0040L □	10A	-	-	DC	control relay	4NO
BF0031L □	10A	-	-	DC	control relay	3NO+1NC
BF0022L □	10A	-	-	DC	control relay	2NO+2NC
BF0004L □	10A	-	-	DC	control relay	4NC

□ Standard extra low DC consumption coil voltages 024/048Vdc

* Standard coil voltages 012/024/048/110/220Vdc