



Recommended hole size

A POSITION



B POSITION



Notes:

- \* Zinc alloy die cast housing and cylinder.
- \* Bright chrome plated standard.
- \* 7 pin tumblers mechanism.
- \* Brass keys with plastic key cover, nickel plated.
- \* Key may be withdrawn in both positions.
- \* Golden plated contacts and terminals.
- \* 1JS-32140A-2200 Positions(on-on) 4 Terminals.
- \* Hex nut mounted.
- \* All keyed alike #3001 standard.
- \* Contact Rating : 3A 125VAC , 2A 250VAC
- \* ROHS compliance.
- \* UL approval.

DATE	02.13.17	SCALE	2:1	UNIT	mm	WT. :	g	REV.:	A	DESCRIPTION	KEY LOCK SWITCH
TOLERANCES	1.0	0.5	0.2	0.1	0.05	0.02	0.01	0.005	0.002		
APPROVED BY		CHECKED BY		DRAWN BY						PART NO.	1JS-32140A-2200
JIN TAY INDUSTRIES CO., LTD.										MATERIAL	
REV. NO.	COORDINATES	WAS	NEW	DATE	BY					NOTE	
1											