



4902 - FEMALE/FEMALE BSP PARALLEL



maximum working pressure	30 bar 3 MPa 435 psi
working temperature	-20 to 130 °C -4 to 266 °F 253 to 403 °K
body	NICKEL PLATED BRASS
retaining nut	NICKEL PLATED BRASS
stem	NICKEL PLATED BRASS
stem seal	PTFE
'O'-rings	PTFE
ball seal	PTFE
handle	TREATED STEEL

Part Nb	C	E (mm)	F (mm)	H (mm)	L (mm)	M (mm)	(kg)
	All	All	All	All	All	All	All
4902 01 45	G4	29	125	154	191	255	9.04
4902 10 13	G1/4	9	20	38	39	82	.131
4902 10 17	G3/8	9	20	38	39	82	.117
4902 15 21	G1/2	11	25	43	50	100	.204
4902 20 27	G3/4	12	31	50	54	120	.329
4902 25 34	G1	14	38	54	67	120	.468
4902 32 42	G1 1/4	15	48	73	77	158	.77
4902 40 49	G1 1/2	17	54	79	90	158	1.04
4902 50 48	G2	19	66	86	106	158	1.76
4902 65 47	G2 1/2	22	85	132	136	255	4.5
4902 80 46	G3	25	99	140	157	255	5.84