

HS LC-V-T-D4X5,2S-45 - Fiber optic



1082300

<https://www.phoenixcontact.com/us/products/1082300>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Vertical 4 mm light guide, transparent, with spherical 5.2 mm raised head, assembly for wall thicknesses from 1 mm, made of polycarbonate (UL 94-V0), installation length 45 mm, watertight, IP68 (EN 50529)

Your advantages

- Light guides are perfectly matched to electronics housings
- Resistance to ESD
- Housing processing available on request
- Enables simple visual status and diagnostic indicators

Commercial Data

Item number	1082300
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	AC05
Product Key	ACGABC
GTIN	4055626812540
Weight per Piece (including packing)	2.1 g
Weight per Piece (excluding packing)	1 g
Customs tariff number	39269097
Country of origin	DE

HS LC-V-T-D4X5,2S-45 - Fiber optic



1082300

<https://www.phoenixcontact.com/us/products/1082300>

Technical Data

Notes

Assembly instruction:	The light guide is designed to be pressed into an H7-tolerated receptacle. Dry-install the LED display by pressing it in vertically. As an alternative, you can glue in the LED display, e.g., using LOCTITE 460.
General	Refer to the data sheet for the range in the download area.

Product properties

Product type	Fiber optic
Number of positions	1
Alignment	Vertical
Type	passive, rigid
Conductor type	Single light guide
Head form	Raised head
Number of indicators	1 (1 row x 1 column)

Electrical properties

ESD protection	< 4 kV
----------------	--------

Dimensions

Length	45 mm
Diameter	5 mm
Hole diameter	4.6 mm ^{H7}

Material specifications

Color	transparent
Color (Light guide)	transparent
Flammability rating according to UL 94	HB
Insulating material	Polycarbonat

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP68
Ambient temperature (operation)	-20 °C ... 50 °C

HS LC-V-T-D4X5,2S-45 - Fiber optic

1082300

<https://www.phoenixcontact.com/us/products/1082300>



Approvals



EAC

Approval ID: B.01687

HS LC-V-T-D4X5,2S-45 - Fiber optic



1082300

<https://www.phoenixcontact.com/us/products/1082300>

Classifications

ECLASS

ECLASS-11.0

27182702

ETIM

ETIM 8.0

EC001031

UNSPSC

UNSPSC 21.0

31261500

HS LC-V-T-D4X5,2S-45 - Fiber optic



1082300

<https://www.phoenixcontact.com/us/products/1082300>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com