

# CRIMPFOX 10T-F - Crimping pliers



1134913

<https://www.phoenixcontact.com/us/products/1134913>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Crimping pliers, type of contact: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, min. cross section: 0.14 mm<sup>2</sup>, max. cross section: 10 mm<sup>2</sup>, For TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, frontal insertion, compression: Trapezoidal crimp, black

## Your advantages

- Large cross section range from 0.14 mm<sup>2</sup> ... 10 mm<sup>2</sup>
- For ferrules up to a length of 18 mm
- Comfortable to use, thanks to low grip span with optimum manual force progression
- Process reliability, thanks to pressure lock and self-adjusting die
- Suitable for TWIN ferrules, thanks to continuous automatic adjustment

## Commercial Data

Item number	1134913
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	BH31
Product Key	BH3131
GTIN	4063151067168
Weight per Piece (including packing)	389.4 g
Weight per Piece (excluding packing)	301.8 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX 10T-F - Crimping pliers



1134913

<https://www.phoenixcontact.com/us/products/1134913>

## Technical Data

### Product properties

Product type	Crimping tool
Compression	Trapezoidal crimp

### Crimping position 1

Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	10 mm <sup>2</sup>
AWG min	26
AWG max	8

### Electrical properties

Fuse	DIN 46228-1, DIN 46228-4
------	--------------------------

### Connection data

#### Conductor connection

Cross section range, metric	0.14 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Cross section range AWG	26 ... 8

### Dimensions

Width	65 mm
Height	25 mm
Length	180 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX 10T-F - Crimping pliers

1134913

<https://www.phoenixcontact.com/us/products/1134913>



## Approvals



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX 10T-F - Crimping pliers



1134913

<https://www.phoenixcontact.com/us/products/1134913>

## Classifications

### ECLASS

ECLASS-9.0	21043811
ECLASS-11.0	21043811

### ETIM

ETIM 8.0	EC000168
----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX 10T-F - Crimping pliers

1134913

<https://www.phoenixcontact.com/us/products/1134913>



## Accessories

### CRIMPFOX/ SPR-4 - Replacement spring

1200288

<https://www.phoenixcontact.com/us/products/1200288>



Spare recuperating spring

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)