




221Series

接线范围/Wire Range:
硬线/solid wire:
0.2-4.0mm²
软线/Strand wire:
0.14-4.0mm²

电压/Voltage:
450V
电流/Current:
32A

Shell : PC
Contact:
Phosphor bronze tin plating
Spring piece:
Stainless steel



型号/Model:
221-412
产品尺寸/LxWxH:
13x19x9.9MM

型号/Model:
221-413
产品尺寸/LxWxH:
18.7x19x9.9MM

型号/Model:
221-414
产品尺寸/LxWxH:
24.3x19x9.9MM


型号/Model:
221-415
产品尺寸/LxWxH:
30x19x9.9MM

手柄颜色，多色可选

Lever button can have more color options.




- Small space consumption
- Protection against electrical shock
- Low installed cost and safe
- Maintenance-free connection
- A reusable connector
- Lever color can be customized



Strip Wire: 10-12mm



Push up lever



Insert conductor and push down lever

