

## Patch panels - VS-PP-F-RJ45-10G - 1403154

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Patch panels, Degree of protection: IP20, Number of positions: 8, Material: PC-GF, Connection method: IDC fast connection

### Why buy this product

- DIN rail mounting



### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 005874
GTIN	4055626005874
Weight per Piece (excluding packing)	1.000 g
Custom tariff number	85369010
Country of origin	Switzerland

### Technical data

#### Mechanical characteristics

Number of positions	8
Number of slots	1
Shielded	yes
Insertion/withdrawal cycles	≥ 750
Connection method	IDC fast connection
Color	gray
Mounting type	DIN rail mounting
Degree of protection	IP20
No. of cable outlets	1

# Patch panels - VS-PP-F-RJ45-10G - 1403154

## Technical data

### Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Degree of protection	IP20

### Material data

Flammability rating according to UL 94	V0
Housing material	PC-GF
Contact carrier material	PC
Contact material	Copper alloy
Contact surface material	Gold over nickel

### Electrical characteristics

Number of positions	8
---------------------	---

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Approvals

### Approvals

Approvals

EAC

Ex Approvals

### Approval details

EAC		B.01742
-----	---	---------

