

Signal lamps with integrated LED - 9.1 mm, round protruding lens

1.02.157.211/1300

With integrated series resistor. Other voltages on request.



General information

Form of lens	round protruding
Color of lens	translucent red
Diameter of collar	11 mm

Dimensions

Overall height	7 mm
Mounting depth	30.5 mm
Mounting hole	9.1 mm

Mechanical design

Mounting	ring nut
Terminals	solder terminals
Lamp socket	T 4.6
Lamp	LED

Electrical characteristics

Operating voltage U_B	24 - 28 V
Input current I_{CC} type.	15 mA

Other specifications

Degree of protection from front side	IP40 (DIN EN 60529)
Weight	2 g
ROHS compliant	yes
REACH compliant	yes

Mounting hole



