




Double-Head Crimping Quick Wiring Connector Series




PCT-2-2



PCT-2-3



PCT-2-4




PCT-2-5



Electrical performance & Material

Model	PCT-2-X(X:number of poles)
Pole	2P 3P 4P 5P
Rated voltage	250V
Rated current	32A
Strip length	8-10mm/0.37in
Wiring size	Solid:0.08~4.0mm ² /12~28AWG Strand:0.08~2.5mm ² /12~14AWG
Wiring method	Crimp
shell	Nylon66 U194 V-0 / PC
Contact	Copper tin plating
Spring	High-performance spring steel
Temperature	-25°C~85°C
Applications	Construction, home improvement, junction box, lamp lighting, motor, power supply



***High-performance spring steel,
Maintains high elasticity even after frequent use**

***Red copper contact, better conductivity**

***Multicolor wrench, easy to distinguish electrodes**

***Wrenches can be customized in monochrome or multicolor**




Double-Head Crimping Quick Wiring Connector Series




PCT-2-2



PCT-2-3



PCT-2-4



PCT-2-5

*Matching splicing accessories

