




222 Seires Lever Crimp Connectors QUICK WIRING CONNECTOR SERIES



Electrical Performance & Material	
Model	PCT-212/213/214/215/218
Number of holes	2.3.4.5.8
Rated Voltage	250V
Rated Current	32A
Strip Length	10-12mm/0.47in
Wiring size	Solid wire: 0.5-4mm ²
	Strand wire: 0.5-2.5mm ²
Wiring Method	Lever Crimp
Shell	Nylon / PC
Contact	Copper
Spring	High-Performance spring steel
Temperature	-25°C-85°C
Applications	Building Wire Branch and connection

Product Appearance Size



How To Use



1) Strip Wire



2) Push Up Lever



3) Insert Conductor
And Push Down Lever

Available Wire Types



Solid



Stranded



Fine Stranded



Tine Stranded
Tip Bonded



Fine Stranded With
Crimp Ferrule



Fine Stranded With
Crimp Pin Terminal